

Numery katalogowe

Poz. 1 Numery katalogowe: AFX2

Rozwidlone stent-grafy AFX®2 BE A 22 – 60 / I 13 40 BE A 22 – 60 / I 16 40 BE A 22 – 70 / I 16 30 BE A 22 – 70 / I 20 30 BE A 22 – 80 / I 16 40 BE A 22 – 80 / I 20 40 BE A 22 – 90 / I 16 30 BE A 22 – 90 / I 20 30 BE A 25 – 60 / I 16 40 BE A 25 – 70 / I 16 30 BE A 25 – 70 / I 20 30 BE A 25 – 80 / I 13 40 BE A 25 – 80 / I 16 40 BE A 25 – 80 / I 20 40 BE A 25 – 90 / I 16 30 BE A 25 – 90 / I 20 30 BE A 25 – 100 / I 16 40 BE A 25 – 100 / I 20 40 BE A 25 – 110 / I 16 30 BE A 25 – 110 / I 20 30 BE A 25 – 120 / I 16 40 BE A 25 – 120 / I 20 40 BE A 28 – 60 / I 16 40 BE A 28 – 70 / I 16 30 BE A 28 – 70 / I 20 30 BE A 28 – 80 / I 16 40 BE A 28 – 80 / I 20 40 BE A 28 – 90 / I 16 30 BE A 28 – 90 / I 20 30 BE A 28 – 100 / I 16 40 BE A 28 – 100 / I 20 40 BE A 28 – 110 / I 16 30 BE A 28 – 110 / I 20 30 BE A 28 – 120 / I 16 40 BE A 28 – 120 / I 20 40	Nadnerkowe przedłużenia aortalne VELA™ A 25 – 25 / C 75 – O 20 V A 25 – 25 / C 95 – O 20 V A 28 – 28 / C 75 – O 20 V A 28 – 28 / C 95 – O 20 V A 34 – 34 / C 80 – O 20 V A 34 – 34 / C 100 – O 20 V
	Podnerkowe przedłużenia aortalne VELA™ A 25 – 25 / C 75 V A 25 – 25 / C 95 V A 28 – 28 / C 75 V A 28 – 28 / C 95 V A 34 – 34 / C 80 V A 34 – 34 / C 100 V
	Elastyczne przedłużenia biodrowe I 16 – 16 / C 55 F SA I 20 – 13 / C 70 F SA I 20 – 13 / C 88 F SA I 20 – 20 / C 55 F SA
	Przedłużenia biodrowe I 16 – 16 / C 88 SA IS* 20 – 25 / C 55 SA IS* 20 – 25 / C 65 SA
	Koszula prowadząca S17-45

Poz. 2 Numery katalogowe: Alto

TV-AB2080-L; TV-AB2380-L; TV-AB2680-L; TV-AB2980-L; TV-AB3480-L; TV-IL141080-I; TV-IL1410100-I;
TV-IL1410120-I; TV-IL1410140-I; TV-IL1410160-I; TV-IL141280-I; TV-IL1412100-I; TV-IL1412120-I;
TV-IL1412140-I; TV-IL1412160-I; TV-IL141480-I; TV-IL1414100-I; TV-IL1414120-I; TV-IL1414140-I;
TV-IL1414160-I; TV-IL141680-I; TV-IL1416100-I; TV-IL1416120-I; TV-IL1416140-I; TV-IL1416160-I;
TV-IL141880-I; TV-IL1418100-I; TV-IL1418120-I; TV-IL1418140-I; TV-IL1418160-I; TV-IL142280-I;
TV-IL1422100-I; TV-IL1422120-I; TV-IL1422140-I; TV-IL1422160-I; TV-IL142880-I; TV-IL1428100-I;
TV-IL1428120-I; TV-IL1428140-I; TV-IL1428160-I; TV-EX101045-I; TV-EX121245-I; TV-EX141445-I;
TV-EX161645-I; TV-EX181845-I; TV-EX222245-I; TV-EX282845-I; TV-CS14-F; TV-AI01-L